


Above Ceiling Air Plenum



Prefer underfloor water piping, but may have to go overhead if piping/ISOBase interference has no ready solution

ISOBase reps say that they know how to deal with this sort of thing

Note: 5 600mm-wide racks ganged together with no gap -> 118 1/8" wide, not 120" wide.



ISOBase plate typically extend 1-2 inch beyond edge of rack enclosure

Min 9-12 " between ISOBase and wall/objects

Check w/ APC re: interference between ISOBase plates and ACRC/ACRP 5xx Series InRow units. Cf NZ MetService DC

Seismic Isolation Plates
<http://isobase.com/>